

Lago Care

16233 The Lago Care bed is a perfect symbiosis of safety and comfort. A low bed position of ± 25 cm reduces the risk of falling to an absolute minimum, whereas the ergonomic working height of ± 80 cm guarantees efficient care.

Carriage

- Highly stable high/low adjustment by means of supporting arms.
- Trendelenburg and reverse Trendelenburg adjustment up to $\pm 16^\circ$.
- Hidden castors $\varnothing 50$ mm with synthetic cover caps, braked 2 per 2.
- Design pedal to activate the brake mechanism.
- The carriage has no actuators, which facilitates its accessibility and possibility to clean.
- The use of a patient lift is perfectly possible.
- The bed can be moved in every position, except in the safety position (= lowest position).

Mattress platform

- Three- or four- (*) section mattress platform.
- The backrest is electrically adjustable up to $\pm 70^\circ$, with auto-regression.
- The knee rest is electrically adjustable up to $\pm 34^\circ$ (in case of 4 sections).
- The footrest is manually adjustable to obtain the Fowler position (in case of 4 sections).
- The legrest is manually adjustable up to $\pm 14^\circ$ (in case of 3 sections).
- The electric manipulation of the mattress platform sections is equipped with a clamp safety.
- The mattress platform consists of rounded steel mattress platform profiles.
- The mattress platform is equipped with openings for patient restraint straps.
- The backrest and footrest are equipped with 2 synthetic mattress holders.
- Telescopic bed extension possible up to 20 cm (not with Pollux sideguards).
- The head end is equipped with 2 cases to install an IV rod or a lifting pole.
- No visible fastening bolts in the foot panel.
- The bed panels are made of solid oven-dried beech (*).
- Round corners to increase the passive safety.

Electric bed manipulations

- The electric functions can be activated by means of a handset.
- The handset is equipped with a preprogrammed sleeping function.
- The handset can be locked using a key combination.
- The optional handset with selective locking system (*) can switch off several functions selectively by means of a magnetic key.

Paneltypes

- Midea (standard)
- Valentino (*)
- Puro (*)
- Felina (*)
- Neo (*) / Lusso (*)

Sideguards

- Pollux (*)
- Trix (*)
- Atmosphere (*)
- Twin (*)


Accessories

We would like to refer to our accessory list.



Dimensions and technical data

- Width: 100,5 cm, Length: 208 cm
- Height variation mattress platform: $\pm 25 - \pm 80$ cm
- Clearance height of the carriage: 137 mm (with a mattress platform height of 42 cm)
- Safe working load: 250 kg
- Weight (without options): 140 kg
- Mattress platform dimensions: 204 x 86 cm
- Mattress dimensions: 195 x 85 cm, thickness: 12 to 15 cm
- Standby consumption: 0,5 W (max. 4,38 kWh/year)



Materials and finishing

- Wood: Beech (solid, veneer), chipboard (melaminated).
- Foam: CMHR- foam (fire-retardant).
- Metal: epoxy-coating RAL 9006 alu.
- Self-lubricating synthetic hinges (= maintenance-free).
- Withstands the common cleaning products and disinfectants.

For more information about the **materials** and **construction**: please ask for our material lists. We would like to refer to our extensive **colour gamut**.

Options

- 4-section steel mattress platform.
- Mattress platform with removable synthetic sections.
- Footrest extension up to 20 cm.
- Bumpers (not possible with Midea)
- Wall spacer.
- Sideguards.
- Illuminated hand switch.
- Hand switch with selective locking system (incl. Trendelenburg).
- Reading lamp.
- Battery.
- Central brake castors $\varnothing 100$ mm, $\varnothing 125$ mm or $\varnothing 150$ mm activated by a brake bracket.
- Brake buzzer (only with central brake).
- 5th castor (only with castors $\varnothing 150$ mm).
- Manual quick release (CPR).

(*) Option

